


FDA COMPLIANT DIAPHRAGM PUMP SOLUTIONS

AIR OPERATED DOUBLE DIAPHRAGM (AODD) PUMP



LOW SHEAR

ELECTROPOLISHED

RUN-DRY CAPABLE

PORTABLE

FDA
COMPLIANT



Option



VERSAMATIC®
PUMPING MADE EASY


AGITASER®
AGITADORES AGITASER S.L.

FDA COMPLIANT FOOD PROCESSING PUMPS

Features & Benefits




Smooth Clean Casting Finish

Electropolished to a surface finish of Ra 125 µ-in (3.175 µ-m). internally & externally



Exclusive Elima-Matic Air Valve System

Delivers excellent On / Off / On reliability, longevity, and efficiency



Clamped Constructions

Quick tear down and reassembly




Extended-life Diaphragms

Integrated plate PTFE & Dome



Chemical Resistance Air Section Materials

Protects against chemical attack during operation and / or the sanitation process




Hygienic Wing Nuts

For easy assembly




Hygienic Tri-Clamp Fluid Connections

For quick disconnect



Dimensionally Interchangeable Pumps, Parts, Air Sections

For seamless upgrades



FDA COMPLIANT FOOD PROCESSING PUMPS

Markets & Applications

Applications: Product Transfer / Tank Over, Filling Lines, Blending and Mixing, and Ingredient Injection




FOOD & BEVERAGE

- Salsa
- Chili
- Soy Sauce
- Beer
- Wine & Spirits
- Juice Concentrates
- Corn Oils / Syrups
- Chocolate
- Syrup
- Cream Soda / Root Beer
- Confectionary Candies
- Poultry (Saline Injection)
- Pickle Relish
- Flavorings
- Pie Filling
- Spaghetti Sauces
- Salad Dressing
- Barbecue Sauces
- Mayonnaise
- Condensed flavorings
- Soup
- Bakeries



PERSONAL CARE

- Hair Gel
- Shampoo
- Soap
- Creams
- Lubricants
- Lotions
- Petroleum Jelly
- Hair Dye
- Laundry Detergents
- Hand Sanitizer
- Fragrances
- Botanical Extraction



E3•3"
76mm

E2•2"
51mm

E4•1½"
38mm

E1•1"
25mm

E5•½"
13mm

FDA COMPLIANT

Technical Specifications




Specifications	Port Size	1/2" (12.7 mm)	1" (25.4 mm)	1.5" (38 mm)	2" (50.8 mm)	3" (76.2 mm)
	Pump Model	E5	E1	E4	E2	E3
	Wetted Material Options	316 SS				
	Air Side material	PP	PP / AL-NP	AL-NP	SS / AL-NP	SS / AL-NP
	Max Flow Rate Per Minute	12 gpm (45.4 lpm)	46 gpm (174.1 lpm)	70 gpm (265 lpm)	185 gpm (700 lpm)	234 gpm (886 lpm)
	Porting Configurations	Suction: Center Horz Discharge: Center Horz	Suction: Center Horz Discharge: Center Horz	Suction: Center Horz Discharge: Center Horz	Suction: Center Horz Discharge: Center Horz	Suction: Center Horz Discharge: Center Horz
	Connection Type	1 1/2" Tri-Clamp	1 1/2" Tri-Clamp	2" Tri-Clamp	2 1/2" Tri-Clamp	3" Tri-Clamp
	Maximum Viscosity, cSt / SSU	cSt - 2,000 SSU -9,400	cSt - 2,000 SSU -9,401	cSt - 90,000 SSU - 415,500	cSt - 90,000 SSU - 415,501	cSt - 90,000 SSU - 415,502
	Maximum Dry Suction Lift	13' (3.9 m)	16' (4.9 m)	15' (4.6 m)	17' (5.1 m)	20' (6.1 m)
	Air Inlet: Port Air Exhaust Port	Inlet: 3/8" NPT Exhaust: 3/8" NPT	Inlet: 3/8" NPT Exhaust: 1/2" NPT	Inlet: 1/2" NPT Exhaust: 3/4" NPT	Inlet: 1/2" NPT (3/4" NPT, SS) Exhaust: 1" NPT	Inlet: 1/2" NPT (3/4" NPT, SS) Exhaust: 1" NPT
	Max Solids Handling	0.063" (1.6 mm)	0.125" (3.2mm)	0.18" (4.76 mm)	0.25" (6.3 mm)	0.375" (9.5 m)
	Max. Displacement per stroke	0.022 gal (0.08 L)	0.09 gal (0.34 L)	0.25 gal (0.95 L)	0.60 gal (2.27 L)	1.36 gal (5.1 L)
	Maximum Air Inlet Pressure	100 psi (6.8 bar)	100 psi (6.8 bar)	125 psi (8.6 bar)	125 psi (8.6 bar)	125 psi (8.6 bar)
	Cleaning / Sanitizing Method	Clean Out of Place (COP)				
	Wetted Casting Surface Finish, Microinches (Micrometers)	Ra 125 µ-in (3.175 µ-m).				
	Diaphragm Material Options	Hytrel, FDA Satoprene, 2-Piece PTFE, IP Bonded PTFE				
	Shipping weight	17 lbs (7.7 kg)	36 lbs (16.3 kg)	57 lbs (25.9 kg)	106 lbs (48.1 kg)	189-239 lbs (86-108.7 kg)
	Height	10.41" (264.41 mm)	14.44" (366.8 mm)	17.33" (440.2 mm)	26.22" (666 mm)	32.01" (813 mm)
	Width	8.20" (208.3 mm)	10.72" (272.4 mm)	16.66" (423.2 mm)	17.18" (436.3 mm)	21.54" (547 mm)
	Depth	8.19" (208.1 mm)	8.13" (206.4 mm)	13.66" (345.0 mm)	13.62" (346 mm)	16.96" (430.7 mm)
	Base to Suction	0.98" (25 mm)	1.56" (39.6 mm)	2.56" (65.0 mm)	1.72" (43.6 mm)	2.31" (58.7 mm)
	Base to Discharge	9.42" (239.3 mm)	13.63" (346.2 mm)	17.33" (440.2 mm)	24.72" (627.9 mm)	29.76" (755.9 mm)

SS-Stainless Steel, AL-NP-Nickle Plated Aluminum, PP-Polypropylene,
See service manual for complete specifications-
*Standard Configuration

FDA COMPLIANT FOOD PROCESSING PUMPS

Features & Benefits

Versamatic is a leader in diaphragm and materials technologies. Since releasing the patented extended life Dome™ diaphragm and TPE-XL (Santoprene®), both AODD industry firsts, Versamatic has been known as an innovative solutions provider. This tradition continues with the release of the FUSION™ PTFE bonded product offering.



FUSION™ Technology

Extended Flex Life

- Oversized integrated plate supports nearly 50% of the diaphragm through the entire dynamic motion
- No outer plate to wear diaphragm or to trap abrasive particles
- Deflection ridges prevent flex points and eliminate radial cracking
- Back up ribs support and guide the diaphragm with each flex

No Leak Paths

- No center hole or torque required, superior leak free operation & installation

Hygienic / Cleanability

- No outer plate to trap particles for easy cleaning and sanitation

Sizes Available:

- ½", 1", 1½", 2" and 3" diaphragms



RUGGED™ Technology

Solids and Slurries Handling

- The oversized outer plates leave less diaphragm exposed to solids in fluid
- Preferred for high suction lift & positive suction conditions
- Support from large diaphragm plates increases flex life in many poor operating conditions

Interchangeable

- 1½", 2", and 3" diaphragms fit into many Wilden® pump units

Sizes Available:


- ½", 1", 1½", 2" and 3" diaphragms

Please consult your distributor or factory experts for additional details.

COMPETITIVE INTERCHANGEABILITY

Pumps, Parts & Upgrade Air Sections

Displacing Wilden® Saniflo® Series



VALUE

- Same footprint and centerline porting dimensions as Wilden® 1 1/2", 2" and 3" FDA Series Sani-Flo™ Series pumps

IMPORTANCE


- Eliminates the cost of pump installation (re-piping / foot pad)

BENEFIT

- Seamless, low cost transitions when converting Wilden's installed base over to value-added Versamatic pump units

Wilden® and Saniflo™ are registered trademarks of Wilden Pump and Engineering Company, a Dover Resources Company. Versamatic and its products are not affiliated with Wilden Pump and Engineering Company. All original equipment manufacturers' names, colors, pictures, descriptions and part numbers are used for identification purposes only.

Air Section Upgrade Kits for Wilden® Pumps



VALUE

- Complete Elima-Matic air section assembly
- Consistent air section design concept
- Low cost rebuild options (air / pilot valve)

IMPORTANCE

- Simple, low cost conversion or update option versus traditional pump rebuild or complete pump sale
- Consistent design compared to Wilden®
- Elima-Matic air valve system delivers overall low cost of ownership

BENEFIT

- Save time and labor compared to purchasing individual components
- Reduced parts inventory, product complexity and training required with consistent air system design

Quality Replacement Parts that fit Wilden® Pumps



VALUE

- Supplying parts that fit Wilden® pumps since 1983
- Most parts ship in 72 hours or less

IMPORTANCE

- Experts in supplying OEM parts for Versamatic and aftermarket parts that fit Wilden®
- Great delivery, expert service, competitive pricing

BENEFIT

- Save time and money on AODD pump parts
- One stop shopping for pumps and parts
- Reduced parts inventory



Fogars de Tordera 65 · Pol. Ind. Bonavista
08916 Badalona (Barcelona) · Spain
+34 93 232 25 09 · www.agitaser.com



VERSAMATIC®



VERSAMATIC.COM



VM_BRO_HighPressurePumps_Rev1121

©Copyright 2022 Warren Rupp, Inc. All Rights Reserved.